



NORTH



EAST



SOUTH

General Notes:

1. For typical equipment mounting heights see "TYPICAL EQUIPMENT MOUNTING HEIGHTS" drawing.
2. MIL-STD-1691 data can only be accessed from the Equipment Plan.

KEY NOTES

1. MOUNT A5145, HOOK, AT 1219 [4'-0"] AFF. PROVIDE 2-A5145'S FOR NAVY PROJECTS ONLY. MOUNT 1-A5145 AT 1219 [4'-0"] AFF AND 1-A5145 AT 1524 [5'-0"] AFF.
2. F3200, CLOCK, IS FOR NAVY PROJECTS AND IS OPTIONAL.
3. P3200, UTR ELECTRONIC LAVATORY, MAY BE USED INSTEAD OF P3100, LAVATORY. FOR THE P3200 PROVIDE EITHER BATTERY POWER OR HARD WIRED CONNECTION.
4. E0906, SUPPLY LOCKER, AND E1500, RAIL, ARE OPTIONAL. LENGTH OF E1500 TO BE DETERMINED BY MANUFACTURER/INSTALLER.
5. VACUUM SLIDE.

EYE, FUNDUS CAMERA ROOM (EYFC1)

OPHTHALMOLOGY/OPTOMETRY

0 1000 2000

ELEVATIONS

11.15 NSM (120 NSF)



DATE: 07/12/2001

1:50 SCALE (MILLIMETERS)